



Saw blade "cordless cut wood - professional", 160x1.6/1.1x20(16), Z24 WZ 22°

- Maximum runtime for cordless saws thanks to extra thin steel blade thickness and cutting width
- Significantly more cuts per battery pack charge compared to standard saw blades with the same long tool life
- Particularly long tool life thanks to best carbide quality and finely-ground teeth
- Precise, low-noise and vibration-minimised cuts thanks to lasered expansion slots (and partially laser ornaments) as well as lasered steel blades made from sintered steel

Order no.	628030000
EAN code	4007430176073
Diameter x cutting width x bore	160 x 1.6 x 20 / 16 mm
Material	HW/CT
Number of teeth	24
Tooth shape	WZ
Steel blade thickness	1.1 mm
Rake angle	22°
Suitable for	KSAP 18 / KSA 18 LTX
Packaging	Cardboard box