



Saw blade "precision cut wood - professional", 220x2.6/1.6x30, Z48 DZ/HZ 10°

- Very wide range of uses in wood processing
- For very good, clean cutting results for longitudinal or cross-cuts in softwood and hardwood
- Perfectly suited for hard wood and plywood, untreated chipboards, coated or veneered, MDF, composite materials
- High power consumption so the saw must have a high performance motor
- Particularly long tool life thanks to best carbide quality and finely-ground teeth
- Precise, low-noise and vibration-minimised cuts thanks to lasered expansion slots (and partially laser ornaments) as well as lasered steel blades made from sintered steel
- Secondary holder for circular saw blades with Ø 216, 250, 254 and over 300 mm

| | |
|---------------------------------|---------------------------|
| Order no. | 628043000 |
| EAN code | 4007430176813 |
| Diameter x cutting width x bore | 220 x 2.6 x 30 mm |
| Material | HW/CT |
| Number of teeth | 48 |
| Tooth shape | DZ/HZ |
| Steel blade thickness | 1.6 mm |
| Rake angle | 10° |
| Suitable for | UK 290 / UK 333 / Secanta |
| Packaging | Cardboard box |