



## Saw blade "precision cut wood - professional", 315x2.8/1.8x30, Z48 WZ 0°

- Very wide range of uses in wood processing
- For very good, clean cutting results for longitudinal or cross-cuts in softwood and hardwood
- Perfectly suited for hard wood and plywood, untreated chipboards, coated or veneered, MDF, composite materials
- High power consumption so the saw must have a high performance motor
- Particularly long tool life thanks to best carbide quality and finely-ground teeth
- Precise, low-noise and vibration-minimised cuts thanks to lasered expansion slots (and partially laser ornaments) as well as lasered steel blades made from sintered steel
- Secondary holder for circular saw blades with Ø 216, 250, 254 and over 300 mm

<b>Order no.</b>	<b>628057000</b>
<b>EAN code</b>	<b>4007430176912</b>
Diameter x cutting width x bore	315 x 2.8 x 30 mm
Material	HW/CT
Number of teeth	48
Tooth shape	WZ
Steel blade thickness	1.8 mm
Rake angle	0°
Suitable for	KGT 300 / TKHS 315
Packaging	Cardboard box