



Saw blade "precision cut wood - professional", 254x2.4/1.6x30, Z40 WZ 20°

- Very wide range of uses in wood processing
- For very good, clean cutting results for longitudinal or cross-cuts in softwood and hardwood
- Perfectly suited for hard wood and plywood, untreated chipboards, coated or veneered, MDF, composite materials
- High power consumption so the saw must have a high performance motor
- Particularly long tool life thanks to best carbide quality and finely-ground teeth
- Precise, low-noise and vibration-minimised cuts thanks to lasered expansion slots (and partially laser ornaments) as well as lasered steel blades made from sintered steel
- Secondary holder for circular saw blades with Ø 216, 250, 254 and over 300 mm

Order no.	628059000
EAN code	4007430229533
Diameter x cutting width x bore	254 x 2.4 x 30 mm
Material	HW/CT
Number of teeth	40
Tooth shape	WZ
Steel blade thickness	1.6 mm
Rake angle	20°
Suitable for	TS 254 / TK 250 / TS 254 M
Packaging	Cardboard box