



## Saw blade "multi cut - professional", 152x2.4/1.6x20, Z54 FZ/TZ 5° neg.

- Universal use for demanding materials
- For the highest standards in cutting quality, e.g. for laminate, thin-walled plastic, aluminium, copper and bronze materials
- Ideally suited for many interior work applications
- Perfect cutting results, also for cross-cuts in solid wood, coarse, coated or veneered chipboards, MDF
- The circular saw must have a very high performance power
- Particularly long tool life thanks to best carbide quality and finely-ground teeth
- Precise, low-noise and vibration-minimised cuts thanks to lasered expansion slots (and partially laser ornaments) as well as lasered steel blades made from sintered steel

Order no.	628070000
EAN code	4007430176370
Diameter x cutting width x bore	152 x 2.4 x 20 mm
Material	HW/CT
Number of teeth	54
Tooth shape	FZ/ TZ
Steel blade thickness	1.6 mm
Rake angle	5° neg.
Suitable for	Ks 0852 S
Packaging	Cardboard box