



Saw blade "power cut wood - professional", 160x2.2/1.4x20, Z30 WZ 5°

- For coarse and semi-fine cuts with continuous feed. Ideal for high feed rate / low power consumption machines
- Good cutting results for straight cuts in solid wood
- Partially suitable for construction wood with nails and concrete residue
- Particularly long tool life thanks to best carbide quality and finely-ground teeth
- Precise, low-noise and vibration-minimised cuts thanks to lasered expansion slots (and partially laser ornaments) as well as lasered steel blades made from sintered steel

| Order no. | 628071000 |
|---------------------------------|--|
| EAN code | 4007430176387 |
| Diameter x cutting width x bore | 160 x 2.2 x 20 mm |
| Material | HW/CT |
| Number of teeth | 30 |
| Tooth shape | WZ |
| Steel blade thickness | 1.4 mm |
| Rake angle | 5° |
| Suitable for | KS 54 / KSE 55 Plus / KSE 55 Vario Plus / KS 55 / KS 55 FS |
| Packaging | Cardboard box |