



Saw blade "multi cut - professional", 190x2.2/1.4x30, Z56 FZ/TZ 8°

- Universal use for demanding materials
- For the highest standards in cutting quality, e.g. for laminate, thin-walled plastic, aluminium, copper and bronze materials
- Ideally suited for many interior work applications
- Perfect cutting results, also for cross-cuts in solid wood, coarse, coated or veneered chipboards, MDF
- The circular saw must have a very high performance power
- Particularly long tool life thanks to best carbide quality and finely-ground teeth
- Precise, low-noise and vibration-minimised cuts thanks to lasered expansion slots (and partially laser ornaments) as well as lasered steel blades made from sintered steel

Order no.	628077000
EAN code	4007430176448
Diameter x cutting width x bore	190 x 2.2 x 30 mm
Material	HW/CT
Number of teeth	56
Tooth shape	FZ/ TZ
Steel blade thickness	1.4 mm
Rake angle	8°
Suitable for	KS 66 / KS 66 Plus / KSE 68 Plus / KS 66 FS
Packaging	Cardboard box