



**Saw blade "multi cut - professional",  
216x2.4/1.8x30, number of teeth 60, Z60 FZ/  
TZ, 5°neg.**

- Universal use for demanding materials
- For the highest standards in cutting quality, e.g. for laminate, thin-walled plastic, aluminium, copper and bronze materials
- Ideally suited for many interior work applications
- Perfect cutting results, also for cross-cuts in solid wood, coarse, coated or veneered chipboards, MDF
- The circular saw must have a very high performance power
- Particularly long tool life thanks to best carbide quality and finely-ground teeth
- Precise, low-noise and vibration-minimised cuts thanks to lasered expansion slots (and partially laser ornaments) as well as lasered steel blades made from sintered steel
- Secondary holder for circular saw blades with Ø 216, 250, 254 and over 300 mm

|                                 |  |
|---------------------------------|--|
| <b>Order no.</b>                | <b>628083000</b>   |
| <b>EAN code</b>                 | <b>4007430176509</b>   |
| Diameter x cutting width x bore | 216 x 2.4 x 30 mm  |
| Material                        | HW/CT  |
| Number of teeth                 | 60   |
| Tooth shape                     | FZ/ TZ   |
| Steel blade thickness           | 1.8 mm   |
| Rake angle                      | 5° neg.  |
| Suitable for                    | KS 216 M Laser-cut / KGS 216 M / KGS 216 Plus / KGSV 216 M / KGSV 72 Xact / KGSV 72 Xact SYM |
| Packaging                       | Cardboard box  |