



Saw blade "multi cut - professional", 315x2.8/2.0x30, Z96 FZ/TZ, 5°neg.

- Universal use for demanding materials
- For the highest standards in cutting quality, e.g. for laminate, thin-walled plastic, aluminium, copper and bronze materials
- Ideally suited for many interior work applications
- Perfect cutting results, also for cross-cuts in solid wood, coarse, coated or veneered chipboards, MDF
- The circular saw must have a very high performance power
- Particularly long tool life thanks to best carbide quality and finely-ground teeth
- Precise, low-noise and vibration-minimised cuts thanks to lasered expansion slots (and partially laser ornaments) as well as lasered steel blades made from sintered steel
- Secondary holder for circular saw blades with Ø 216, 250, 254 and over 300 mm

Order no.	628092000
EAN code	4007430177056
Diameter x cutting width x bore	315 x 2.8 x 30 mm
Material	HW/CT
Number of teeth	96
Tooth shape	FZ/ TZ
Steel blade thickness	2 mm
Rake angle	5° neg.
Suitable for	KGS 315 Plus
Packaging	Cardboard box