



## Saw blade "multi cut - professional", 254x2.4/1.6x30, Z80 FZ/TZ, 5°

- Universal use for demanding materials
- For the highest standards in cutting quality, e.g. for laminate, thin-walled plastic, aluminium, copper and bronze materials
- Ideally suited for many interior work applications
- Perfect cutting results, also for cross-cuts in solid wood, coarse, coated or veneered chipboards, MDF
- The circular saw must have a very high performance power
- Particularly long tool life thanks to best carbide quality and finely-ground teeth
- Precise, low-noise and vibration-minimised cuts thanks to lasered expansion slots (and partially laser ornaments) as well as lasered steel blades made from sintered steel
- Secondary holder for circular saw blades with Ø 216, 250, 254 and over 300 mm

<b>Order no.</b>	<b>628093000</b>
<b>EAN code</b>	<b>4007430229540</b>
Diameter x cutting width x bore	254 x 2.4 x 30 mm
Material	HW/CT
Number of teeth	80
Tooth shape	FZ/ TZ
Steel blade thickness	1.6 mm
Rake angle	5°
Suitable for	TS 254 / TK 250 / TS 254 M
Packaging	Cardboard box