



Saw blade "power cut wood - professional", 254x2.4/1.8x30, Z24 WZ 5° neg.

- For coarse and semi-fine cuts with continuous feed. Ideal for high feed rate / low power consumption machines
- Good cutting results for straight cuts in solid wood
- Partially suitable for construction wood with nails and concrete residue
- Particularly long tool life thanks to best carbide quality and finely-ground teeth
- Precise, low-noise and vibration-minimised cuts thanks to lasered expansion slots (and partially laser ornaments) as well as lasered steel blades made from sintered steel
- Secondary holder for circular saw blades with Ø 216, 250, 254 and over 300 mm

Order no.	628220000
EAN code	4007430190307
Diameter x cutting width x bore	254 x 2.4 x 30 mm
Material	HW/CT
Number of teeth	24
Tooth shape	WZ
Steel blade thickness	1.8 mm
Rake angle	5° neg.
Suitable for	KS 254 Plus / KGS 254 M / KGS 254 Plus / KGS 254 I Plus
Packaging	Cardboard box