



Diamond channeling disc 3, 125x28.5x22.23mm, "professional", "UP", universal

- Fast and comfortable cutting of wall slots in different materials possible
- Highly reduced workload thanks to the intelligent system of interlacing arrangement of segments, since chiseling away of the centre is not required. Great time saving thanks to cutting in one step.
- Reduction of dirt and dust, since the material is removed cleanly and completely from the slot
- Customised slots for individual lines, or for Ø 20 and 25 mm-empty pipes. Max. cutting width: 20 mm (2 rows 628298000) / 30 mm (3 rows 628299000)

Order no.	628299000
EAN code	4007430330826
Diameter x bore	125 x 22.23 mm // 5 x 7/8 "
Segment dimensions	28.5 x 7 mm // 1 1/8 x 0.275 "
Number of segments	30
Maximum speed	12200 rpm
Sales unit	1
Packaging	Cardboard box