



**Aluminium oxide mounted point 50 x 10 x
40 mm, shank 6 mm, K 24, cylinder**

- Mounted points made of aluminium oxide for processing stainless steel, Inox, NK 24 N BA, soft version, free from iron and sulphur
- For the preparation of weld seams, processing of weld seams
- Rough machining to fine processing
- For deburring and buffing

Order no.	62834000
EAN code	4007430228697
Head Ø	50 mm
Working length	10 mm
Overall length	40 mm
Shaft Ø	6 mm
Grit	K 24