



Saw blade "power cut wood - professional", 235x2.6/1.8x30, Z24 WZ 20°

- For coarse and semi-fine cuts with continuous feed. Ideal for high feed rate / low power consumption machines
- Good cutting results for straight cuts in solid wood
- Partially suitable for construction wood with nails and concrete residue
- Particularly long tool life thanks to best carbide quality and finely-ground teeth
- Precise, low-noise and vibration-minimised cuts thanks to lasered expansion slots (and partially laser ornaments) as well as lasered steel blades made from sintered steel

Order no.	628493000
EAN code	4061792188518
Diameter x cutting width x bore	235 x 2.6 x 30 mm
Material	HW/CT
Number of teeth	24
Tooth shape	WZ
Steel blade thickness	1.8 mm
Rake angle	20°
Suitable for	KS 85 FS
Packaging	Cardboard box