



Saw blade "cordless cut wood - professional", 305x2.2/1.8x30, Z56 WZ 5° neg.

- Maximum runtime for cordless saws thanks to extra thin steel blade thickness and cutting width
- Significantly more cuts per battery pack charge compared to standard saw blades with the same long tool life
- Particularly long tool life thanks to best carbide quality and finely-ground teeth
- Precise, low-noise and vibration-minimised cuts thanks to lasered expansion slots (and partially laser ornaments) as well as lasered steel blades made from sintered steel
- Secondary holder for circular saw blades with Ø 216

Order no.	628695000
EAN code	4061792238718
Diameter x cutting width x bore	305 x 2.2 x 30 mm
Material	HW/CT
Number of teeth	56
Tooth shape	WZ
Steel blade thickness	1.8 mm
Rake angle	5° neg.
Packaging	Cardboard box