



**Compressed air hose ISO 9 mm x 14 mm /  
10 m**

- For all normal applications
- With quick-action coupling and nipple

<b>Order no.</b>	<b>628781000</b>
<b>EAN code</b>	<b>4007430267511</b>
Length	10 m
Inner Ø	9 mm
Outer Ø	14 mm
Maximum pressure	20 bar
Profile	ISO
Version	With quick-action coupling and nipple