



## Screw-type angle attachment 57 Nm

- Screw-type angle attachment for professional use.
- Suitable for cordless screwdrivers up to a maximum of 57 Nm and a maximum of 2,000 rpm
- Width across corners only 50 mm
- Bit holder with quick-action coupling
- With 1/4" (6.35 mm) hexagonal shank
- Gears made of special steel
- Suitable for forward and reverse rotation
- Support handle adjustable to 12 positions with lockable push-button
- Screw-type angle attachment with 105° inclination
- For inserting screws more easily into places difficult to reach

Order no.  
EAN code

630463000  
4007430157300