



Flexible shaft 30980

- Suitable for speeds of 7,500 to 30,000 rpm
- Bearing-mounted at both ends
- For router bits, mounted points, lamellar grinding wheels etc. with 8 mm shaft diameter. Interchangeable collet for accessories with 6 mm shaft diameter (630977000) and 3 mm shaft diameter (630976000) available as accessory
- 8 mm driving shaft for fixing the flexible shaft in the collet bore of the drive machine. If the collet bore of the drive machine has a different dimension than 8 mm, the collet of the drive machine must be changed. 6 mm collet available as accessory (631945000)

Order no.	630980000
EAN code	4007430423689
Suitable for routers	FME 737
Suitable for die grinders	G 400 / GE 710 Compact / GE 710 Plus / GE 950 G Plus / GA 18 LTX
Length	1.3 m / 4 ft
Driving shaft	8 mm / 5/16 "
Collet bore	8 mm
Weight	0.8 kg / 1.76 lbs