



**Suction hose, Ø 32 mm, length 3.5 m, for  
ASA 25 L PC, ASA 30 L PC Inox**

- Hose length 3.5 m (not anti-static) incl. handle adapter and coupling bush with shunt air opening
- Standard equipment for ASA 25 L PC and ASA 30 L PC Inox
- With Ø 58 mm connector and Ø 35 mm

Order no.	631337000
EAN code	4007430249852
Hose length	3.5 m / 10 ft
Hose-Ø, internal	32 mm / 1 1/4 "
Hose-Ø, external	40 mm / 1.56 "
Connection-Ø, external	27 mm / 1.06 "
Anti-static	0
Conducts electricity	0
Bayonet connection	0
Rotating adapter	on both sides