



SDS-plus Pro 4 Premium- hammer drill bit / 25.0 x 450 mm

- Intelligent geometry with its uncompromised quality of detail ensures a long service life, precise drill holes and maximum quiet running - even on the toughest loads.
- Highest level of safety thanks to the optimum symmetrical head geometry with 4 full carbide cutters, which do not catch when encountering reinforcing.
- Up to Ø 16 mm: with innovative, welded full carbide head for maximum tool life and larger dust outputs for highest drill speed
- Power breakers cause micro tears in the material for a noticeable quicker drill progress
- Low-vibration drilling with 4-spiral helix. 2 large volume helixes remove the bore dust quickly and reliably from the drill hole, two reinforced spirals ensure additional safety and stability.
- Extremely resistant to breakage thanks to high-grade special steel
- Very long tool life for up to 50% more dowel-compatible circular bores
- For professional use in masonry, concrete and armoured concrete

Order no.	631710000
EAN code	4007430436863

Diameter	25 mm
Working length	400 mm
Overall length	450 mm
Sales unit	1