



SDS-Plus Pro 4 hammer drill bit / 12.0 x 1000 mm

- Highest drill speed thanks to reduction in friction and improved impact transmission thanks to the special cutting geometry on the chisel-shaped drill head.
- Stable and durable centering point for high-precision spot-drilling
- Power breakers cause micro tears in the material for a noticeable quicker drill progress
- The probability of snagging on concrete reinforcements is significantly reduced thanks to enlarged armouring phases.
- The 2-spiral helix with its helical geometry with reinforced core ensures quick delivery of bore dust and maximum breakage resistance
- For use in concrete, masonry, natural stone, granite

| | |
|------------------|----------------------|
| Order no. | 631797000 |
| EAN code | 4007430444790 |

| | |
|----------------|---------|
| Diameter | 12 mm |
| Working length | 950 mm |
| Overall length | 1000 mm |
| Sales unit | 1 |