



## SDS-Plus Pro 4-hammer drill bit / 16.0 x 1,000 mm

- Highest drill speed thanks to reduction in friction and improved impact transmission thanks to the special cutting geometry on the chisel-shaped drill head.
- Stable and durable centering point for high-precision spot-drilling
- Power breakers cause micro tears in the material for a noticeable quicker drill progress
- The probability of snagging on concrete reinforcements is significantly reduced thanks to enlarged armouring phases.
- The 2-spiral helix with its helical geometry with reinforced core ensures quick delivery of bore dust and maximum breakage resistance
- For use in concrete, masonry, natural stone, granite

<b>Order no.</b>	<b>631805000</b>
<b>EAN code</b>	<b>4007430444714</b>
Diameter	16 mm
Working length	950 mm
Overall length	1000 mm
Sales unit	1