



Futuro Top keyless chuck, 10 mm, 3/8"

- The first impact-proof keyless chuck, with integrated spring-loaded bit clamping mechanism and dual dust protection
- Keyless for quick tool change
- Firm grip of clamped tools even under the toughest loads
- The oil-resistant, hard-wearing rubber bellows system protects the thread and the precision press fit from dust and dirt
- For clockwise rotating drills only

Order no.	636215000
EAN code	4007430428516

Clamping width	1 - 10 mm // 1/32 - 3/8 "
----------------	---------------------------

Female thread	3/8" - 24 UNF
---------------	---------------

Outer Ø	42.8 mm / 1.69 "
---------	------------------

Length (closed)	77 mm / 3.03 "
-----------------	----------------

Weight	0.35 kg / 0.77 lbs
--------	--------------------