

Product information

00 21 20 LE

Tool Case "Vision24" Empty



- Max. payload: 20 kg
- Volume: 24 litres
- Without tools
- Flexible options due to the individual partitioning of the inserts in the 60 mm deep base tray and its cover plate with six large tool compartments
- Tough ratchet hinges hold the lid open where necessary despite the deadweight of the tools
- Sturdy, ergonomic carrying handle, snaps into place at a 90° angle
- Removable tool board with 15 tool pockets on the base side and six tool pockets as well as a clamp compartment (400 mm wide) on the cover side, held by a push button
- Two lockable steel flip locks protect the case contents from theft
- With circumferential double aluminium frame
- Heavy duty ABS material, black
- Cover and tool boards made from dirt-repellent PP twin-wall sheets
- External dimensions (W x H x D): 480 x 380 x 180 mm; internal dimensions (W x H x D): 460 x 310 x 170 mm

General	
Article No.	00 21 20 LE
EAN	4003773044567
Weight	4,485 g
Dimensions	173 x 360 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details	
Dimension exterior (interior) width mm	480 mm (460 mm)
Dimension exterior (interior) height mm	175 mm (170 mm)
Dimension exterior (interior) depth mm	370 mm (310 mm)

technical change and errors excepted

Con-Pearl® is a registered trade mark of friedola TECH GmbH