

Product information

00 21 36

Tool Case "Robust34" Electric



- Equipped with 26 brand tools, partly VDE-tested according to DIN EN 60900
- Max. payload: 25 kg
- Volume: 34 litres
- For the toughest conditions: Dust-tight, waterproof and temperatureresistant
- Equipped with 26 brand tools; some VDE tested in accordance with DIN EN/IEC 60900
- Document compartment; tool boards made from dirt-repelling twin-wall PP sheet with space for 42 tool pockets and 67 tool straps
- · Base tray with aluminium separators
- External dimensions (W x H x D): 510 x 419 x 215 mm; internal dimensions (W x H x D):480 x 356 x 199 mm
- Fit-to-fly case, made from impact-resistant polypropylene
- Dustproof and watertight
- Air pressure compensation valve
- Temperature-resistant from 30°C to +80° C
- · Padlock eyelets
- Document compartment; tool boards made from dirt-repelling twin-wall PP sheet with tool pockets and tool straps
- Lockable base tray can be individually divided using aluminium separator system
- Ergonomic dual-component handle
- With a total of 93 inserting options



General	
Article No.	00 21 36
EAN	4003773082583
Weight	8,810 g
Dimensions	419 x 215 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details	
Dimension exterior (interior) width mm	510 mm (480 mm)
Dimension exterior (interior) height mm	215 mm (199 mm)
Dimension exterior (interior) depth mm	419 mm (356 mm)

technical change and errors excepted



With document compartment