

## Product information

# 00 31 30 BK V03

## Electrical Set








- Wide-ranging team: Stripping, gripping, cutting
- High-quality VDE tools in a set for professionals in the electrical industry
- With universal Insulation Stripper, versatile Diagonal Cutter and flexible Stork Beak Gripping Pliers
- Set of three perfectly complementary pliers for all electrical installations
- KNIPEX Insulation Stripper 11 06 160 VDE with opening spring:
- Adaptable: For single, multiple and fine stranded conductors with plastic or rubber insulation up to Ø 5.0 mm or 10 mm<sup>2</sup>; forged from special tool steel; oil-hardened
- KNIPEX Diagonal Cutter 70 06 160 VDE:
- Versatile: Also for hard wire up to Ø 2 mm, clean cut even at the tips; vanadium electric steel, forged, multi stage oil-hardened
- KNIPEX Stork Beak Pliers 26 16 200 VDE:
- Flexible: Snipe Nose Side Cutting Pliers with distortion-tolerant, elastic precision tips; vanadium electric steel, forged, multi stage oil-hardened

### General

Article No.	00 31 30 BK V03
EAN	4003773087885
Weight	618 g
Dimensions	185 x 30 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

### Content

11 06 160	1 x Insulation Stripper with opening spring, universal (Ø 5,0 mm / 10,0 mm <sup>2</sup> ) ⚠ 1000V 
26 16 200	1 x Snipe Nose Side Cutting Pliers (Stork Beak Pliers) ⚠ 1000V   
70 06 160	1 x Diagonal Cutter ⚠ 1000V 

technical change and errors excepted