

Product information

02 02 225

High Leverage Combination Pliers

DIN ISO 5746



- 35 % less effort required than with conventional combination pliers
- With cutting edges (hardness approx. 63 HRC) for heavy duty
- Easier work due to optimised leverage
- Easier cutting, powerful gripping, bending and pulling
- Long cutting edges for thicker cables
- With gripping zones for flat and round material, suitable for versatile use
- Precise, minimal light gap between the gripping jaws to ensure optimal function of the cutting edges
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 63 HRC
- High-grade special tool steel, forged, multi stage oil-hardened

General

Article No.	02 02 225
EAN	4003773043379
Pliers	black atramentized
Head	polished
Handles	with multi-component grips
Weight	405 g
Dimensions	225 x 54 x 23 mm
Standard	DIN ISO 5746
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Cutting capacities hard wire (diameter)	Ø 3.0 mm
Cutting capacities piano wire (diameter)	Ø 2.5 mm
Cutting capacity copper cable, multiple-stranded	Ø 14.0 mm
Cutting capacity copper cable, multiple-stranded	25.0 mm ²

technical change and errors excepted



