

Product information

09 05 240

Lineman's Pliers

American style

DIN ISO 5746 ASME B107.20



- High transmission ratio for easy cutting
- Requires 50 % less effort compared with conventional combination pliers thanks to optimised transmission ratio
- Solid construction for heaviest strain; universally applicable
- Ergonomically optimised handle shape for firm contact to the hand and fatigue reducing operation
- Particularly effective cross-hatched knurled gripping zone in the jaws - for strong gripping and pulling
- Additional gripping zone below the joint for powerful leverage and pressing performance
- With cutting edges for soft and hard wire
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 62 HRC
- Vanadium electric steel, forged, multi stage oil-hardened

General

Article No.	09 05 240
EAN	4003773087380
Pliers	chrome-plated
Head	chrome-plated
Handles	with multi-component grips
Weight	460 g
Dimensions	240 x 55 x 22 mm
Standard	DIN ISO 5746 ASME B107.20
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Cutting capacities medium hard wire (diameter)	Ø 4.6 mm
Cutting capacities hard wire (diameter)	Ø 3.0 mm

technical change and errors excepted