

## Product information

# 11 06 160 T

## Insulation Stripper

With opening spring, universal

IEC 60900 DIN EN 60900

- Pliers with integrated, insulated tether attachment point for a tool tether
- For single, multiple and fine stranded conductors with plastic or rubber insulation up to Ø 5.0 mm or 10 mm<sup>2</sup>
- Easy adjustment to the required diameter of solid or stranded wire with knurled screw and lock nut
- Special tool steel, forged, oil-hardened



⚠ 1000 V 



### General

Article No.	11 06 160 T
EAN	4003773081418
Pliers	chrome-plated
Head	chrome-plated
Handles	insulated with multi-component grips, VDE-tested with integrated insulated tether attachment point for a tool tether
Weight	180 g
Dimensions	160 x 100 x 27 mm
Standard	DIN EN 60900 IEC 60900
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

### Technical details

Stripping capacities in square millimetres	10 mm <sup>2</sup>
Stripping capacities (diameter)	Ø 5.0 mm
AWG	8
Drop Protection System	yes
VDE tested	yes

*technical change and errors excepted*

