

Product information

11 07 160

Insulation Stripper

With opening spring, universal

IEC 60900 DIN EN 60900



£1000V MM

General

Article No. 11 07 160 EAN 4003773015499 Pliers chrome-plated Head chrome-plated Handles with dipped insulation, VDE-tested Weight 205 g Dimensions 160 x 94 x 28 mm Standard DIN EN 60900 IEC 60900 **REACH** compliant does not contain SVHC **RoHS** compliant not applicable **Technical details** Stripping capacities in square millimetres 10 mm² Stripping capacities (diameter) Ø 5.0 mm AWG 8

yes

VDE tested

technical change and errors excepted

- For single, multiple and fine stranded conductors with plastic or rubber insulation up to Ø 5.0 mm or 10 mm²
- Easy adjustment to the required diameter of solid or stranded wire with knurled screw and lock nut
- Special tool steel, forged, oil-hardened