

Product information

12 49 04

Torsion spring

For 12 40/50 200



- For single, multiple and fine stranded conductors with plastic or rubber insulation
- Adapts automatically to the respective cable cross-section; prevents damage to the conductor
- Cutting depth can be adjusted for different insulation materials
- With wire cutter for copper and aluminium wires, multiple stranded up to 10 mm² and single stranded up to 6 mm²
- Smoothly operating mechanism
- Stripping blades and clamping jaws easily replaceable
- Low weight
- Body: glass fibre reinforced plastic
- Blade: special tool steel, oil-hardened

| General | |
|-----------------|-----------------------|
| Article No. | 12 49 04 |
| EAN | 4003773053071 |
| Weight | 4 g |
| Dimensions | 13 x 5 mm |
| REACH compliant | does not contain SVHC |
| RoHS compliant | not applicable |

technical change and errors excepted