

Product information

12 62 180

Automatic Insulation Stripper




- Strips cables with standard materials without any need for manual adjustment
- Fine adjustable zero correction of the blade setting to special material requirements, e.g. due to large temperature differences
- Compact, handy and lightweight tool for common cable cross-sections and insulating materials
- For single, multiple and fine stranded cables of 0.2 up to 6 mm² with standard insulation
- Narrow head style for use in confined areas
- With wire cutter for copper and aluminium wires up to 2.5 mm²
- With adjustable length stop from 6.0 18.0 mm for constant stripping lengths
- Body: glass fibre reinforced plastic
- Blades: special tool steel, oil-hardened, interchangeable

MM

General	
Article No.	12 62 180
EAN	4003773054573
Weight	151 g
Dimensions	180 x 75 x 21 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details	
Stripping capacities in square millimetres	0.2 — 6.0 mm ²
AWG	24 — 10

technical change and errors excepted



KNIPEX Quality – Made in Germany



