

Product information

13 42 165

Stripping Pliers





- Multifunctional cutting and stripping with one pair of pliers
- For time-saving stripping of all round sheathed and damp-proof installation cables (e.g. NYM cable)
- Simplified access especially into deep mounted junction boxes thanks to slim head design and optimally angled cable sheath cutter
- Strip cables easily and without damage thanks to circular cutting edge with depth limiter
- Suitable for universal use: precision wire stripping holes for conductors from 1.5 and 2.5 mm²
- With side cutters for cutting and trimming conductors, wires, small persua and poils.
- All cutters additionally induction-hardened to approx. 61 HRC for high wear resistance
- 30 % lighter than comparable pliers
- · Vanadium electric steel, forged, multi stage oil-hardened



General	
Article No.	13 42 165
EAN	4003773079675
Pliers	black atramentized
Head	polished
Handles	with multi-component grips
Weight	176 g
Dimensions	165 x 57 x 20 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details	
Cutting capacities medium hard wire (diameter)	Ø 3.2 mm
Cutting capacities hard wire (diameter)	Ø 2.2 mm
Cable stripping values (diameter)	8 – 13 mm
Stripping capacities in square millimetres	0.75 — 1.5 mm² / 2.5 mm²

technical change and errors excepted




Cutting of cables of up to Ø 13 mm



wire stripping holes for 1.5 and 2.5 mm² conductors

KNIPEX Quality – Made in Germany





Cutting when shortening single conductors