

#### **Product information**

### 13 72 8

### **KNIPEX WireStripper**

Multifunction Electrician Pliers American style



- Strip faster: precise positioning of the wire thanks to location ridges
- Innovative cutting edge geometry, particularly powerful cutting edges:
  50 % higher cutting capacity and 25 % less cutting effort compared to standard wire strippers
- Fast, burr-free cutting of threaded rods and screws of UNC 6-32 and 8-32 up to class 4.6
- Precisely ground: Stripping profiles for conductors from 18-10 AWG(solid) and 20-12 AWG (finely stranded)
- Easy cutting of copper and aluminium cables up to Ø 15 mm (1/2")
- Multifunctional gripping surfaces for reliable gripping, holding and bending of flat and round material as well as for twisting wires
- High stability and good accessibility thanks to hybrid tips on the pliers head, which are flat and wide
- Convenient: comfortable opening width and ergonomic handle shape, integrated opening spring makes frequent cutting easier
- Ideal for right- and left-handed users: locking device can be operated from either side
- Clear-cut outside edges on the jaws for working on flush-mounted junction boxes and deburring feed-through holes
- · High-grade special tool steel, forged, multi stage oil-hardened

General	
Article No.	13 72 8
EAN	4003773086680
Pliers	black atramentized
Head	polished
Handles	with multi-component grips
Weight	285 g
Dimensions	200 x 55 x 21 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details	
Cutting capacity copper cable, multiple- stranded	Ø 15 mm
Cutting capacity copper cable, multiple- stranded	1/2 Inch
AWG	20 — 10

technical change and errors excepted





# **KNIPEX** Quality – Made in Germany















# **KNIPEX** Quality – Made in Germany













