

Product information

25 02 160

Snipe Nose Side Cutting Pliers

(Radio Pliers)

DIN ISO 5745

- Suitable for finer gripping and cutting work
- Half-round, long, tapered jaws Knurled gripping surfaces
- With cutting edges for soft, medium-hard and hard wire
- Cutting edges additionally induction-hardened, cutting edge hardness
- Straight jaws
- Vanadium electric steel, forged, multi stage oil-hardened






General	
Article No.	25 02 160
EAN	4003773023166
Pliers	black atramentized
Head	polished
Handles	with multi-component grips
Weight	144 g
Dimensions	160 x 55 x 19 mm
Standard	DIN ISO 5745
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details	
Cutting capacities medium hard wire (diameter)	Ø 2.5 mm
Cutting capacities hard wire (diameter)	Ø 1.6 mm
Jaw thickness (joint) (T1)	9.0 mm
Tips width (W4)	3.0 mm
Tips thickness (T2)	2.5 mm
Jaw length (L3)	50.0 mm
Head width (W3)	16.5 mm

KNIPEX Quality – Made in Germany



Technical details



technical change and errors excepted



