

Product information

31 15 160

Flat Nose Pliers

(Needle-Nose Pliers)




- Precision pliers for very exact assembly, bending and adjusting work
- With extra long jaws: length of jaws 55.0 mm
- Smooth ground gripping surfaces
- Edges carefully deburred
- Straight jaws
- Chrome vanadium electric steel, forged, oil-hardened

-	

General		
Article No.	31 15 160	
EAN	4003773016465	
Pliers	chrome-plated	
Head	chrome-plated	
Handles	with multi-component grips	
Weight	124 g	
Dimensions	160 x 56 x 19 mm	
REACH compliant	does not contain SVHC	
RoHS compliant	not applicable	

Technical details	
Jaw thickness (joint) (T1)	7.5 mm
Tips width (W4)	1.8 mm
Tips thickness (T2)	2.5 mm
Jaw length (L3)	55.0 mm
Head width (W3)	16.0 mm



technical change and errors excepted