

Product information

32 11 135

Relay Adjusting Pliers




- For gripping components and wires of the smallest diameters and for bending contact and relay springs Polished gripping surfaces
- Edges carefully deburred
- Flat, concave and pointed jaws
- High-grade special tool steel, forged, oil-hardened

	· She	Mr. W.
		The same of

General		
Article No.	32 11 135	
EAN	4003773035091	
Pliers	black atramentized	
Head	polished	
Handles	plastic coated	
Weight	73 g	
Dimensions	135 x 55 x 12 mm	
REACH compliant	does not contain SVHC	
RoHS compliant	not applicable	

Technical details	
Jaw thickness (joint) (D)	7.0 mm
Tips width (E)	1.0 mm
Tips thickness (F)	1.5 mm
Jaw length (B)	34.0 mm
Head width (A)	12.5 mm



technical change and errors excepted