

Product information

35 32 115

Electronics Pliers

DIN ISO 9655




- Precision pliers for fine assembly work, e g. in electronics and fine mechanics
- For gripping, holding and bending
- Sturdy, zero backlash box joint
- Smooth ground gripping surfacesEdges carefully deburred
- Low-friction double spring for gentle and even opening
- The polish or mirror polish together with a fine film of oil offer effective rust protection - no circuit faults caused by peeling chrome from plated tools
- Round, pointed jaws
- Ball bearing chrome steel, oil hardened

MC 8

General

Article No.	35 32 115	
EAN	4003773035121	
Head	mirror polished	
Handles	with multi-component grips	
Weight	70 g	
Dimensions	115 x 70 x 17 mm	
Standard	DIN ISO 9655	
REACH compliant	does not contain SVHC	
RoHS compliant	not applicable	
Technical details		
Jaw length (B)	22.5 mm	
Jaw thickness (joint) (D)	6.5 mm	
Tips width (E)	2.0 mm	
Tips thickness (F)	1.0 mm	
Head width (A)	11.0 mm	



technical change and errors excepted

KNIPEX Quality – Made in Germany



