

Product information

35 62 145

Electronics Pliers

DIN ISO 9655




- Precision pliers for fine assembly work, e.g. in electronics and fine mechanics
- For gripping, holding and bending
- Sturdy, zero backlash box joint
- Smooth ground gripping surfaces
- Edges carefully deburred
- Low-friction double spring for gentle and even opening
- The polish or mirror polish together with a fine film of oil offer effective rust protection - no circuit faults caused by peeling chrome from plated tools
- Half-round, long jaws
- Ball bearing chrome steel, oil hardened



General	
Article No.	35 62 145
EAN	4003773039556
Head	mirror polished
Handles	with multi-component grips
Weight	103 g
Dimensions	145 x 60 x 19 mm
Standard	DIN ISO 9655
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details	
Jaw length (B)	40.0 mm
Jaw thickness (joint) (D)	7.5 mm
Tips width (E)	2.5 mm
Tips thickness (F)	1.5 mm
Head width (A)	12.0 mm



technical change and errors excepted