

Product information


44 31 J12

- Solid style, forged
- Non-slip, solid tips
- On basis of DIN 5256 C and DIN 5256 C, but bent 45°
- Pliers body and tips: chrome vanadium steel, forged, oil-hardened

Circlip Pliers

For internal circlips in bore holes
45° bent



 45°

General	
Article No.	44 31 J12
EAN	4003773066958
Pliers	black atramentized
Head	polished
Handles	plastic coated
Weight	90 g
Dimensions	140 x 47 x 12 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable
Technical details	
Size of bore	Ø 12 – 25 mm
Tips (diameter)	Ø 1.3 mm

technical change and errors excepted