

Product information

44 31 J32

Circlip Pliers

For internal circlips in bore holes 45° bent



℃<u>∡4</u>5°

- · Solid style, forged
- Non-slip, solid tips On basis of DIN 5256 C and DIN 5256 C, but bent 45°
- Pliers body and tips: chrome vanadium steel, forged, oil-hardened

General	
Article No.	44 31 J32
EAN	4003773066972
Pliers	black atramentized
Head	polished
Handles	plastic coated
Weight	195 g
Dimensions	225 x 45 x 14 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details	
Size of bore	Ø 40 – 100 mm
Tips (diameter)	Ø 2.3 mm

technical change and errors excepted