

Product information

48 31 J0

Precision Circlip Pliers

For internal circlips in bore holes

With overstretching limiter

DIN 5256 C



- Heavy duty in continuous operation: up to 10 times longer service life compared to turned tips
- With inserted tips for reliable work
- With overexpansion guard (adjustable using end stop)
- Adjustment using hexagonal screw
- Ideal for series production as excessive expansion of rings is effectively prevented
- Bolted joint: precise, zero backlash operation of pliers
- Non-slip plastic coating on the handles
- DIN 5256 C, straight tips
- With overstretching limiter for standardised assembly in accordance with DIN 472
- The adjustable stop screw prevents the rings from overstretching
- Inserted tips: spring steel wire, drawn
- Pliers body: chrome vanadium electric steel, forged, oil-hardened



General	
Article No.	48 31 J0
EAN	4003773079552
Pliers	grey atramentized
Handles	with non-slip plastic coating
Weight	105 g
Dimensions	140 x 52 x 11 mm
Standard	DIN 5256 C
REACH compliant	does not contain SVHC
RoHS compliant	not applicable
Technical details	
Size of bore	Ø 8 – 13 mm
Tips (diameter)	Ø 0.9 mm

technical change and errors excepted

