

Product information

49 41 A31

Precision Circlip Pliers

For external circlips on shafts

DIN 5254 B



- Heavy duty in continuous operation: up to 10 times longer service life compared to turned tips
- With inserted tips for reliable work
- Heavy duty under continuous use; up to 10 times longer service life
- Precise, smoothly-operating screw joint
- Forged
- Large contact faces on the tips: no distortion of circlips, easy fitting
- Slim head style allows use in confined areas
- Internal opening spring, protected and captive
- Handles with non-slip plastic coating
- DIN 5254 B; 90° angled tips
- With overstretching limiter for standardised assembly in accordance with DIN 471
- The adjustable stop screw prevents the rings from overstretching
- Inserted tips: spring steel wire, drawn
- Pliers body: chrome vanadium electric steel, forged, oil-hardened

MM  90°



General

| | |
|-----------------|-------------------------------|
| Article No. | 49 41 A31 |
| EAN | 4003773079620 |
| Pliers | grey atramentized |
| Handles | with non-slip plastic coating |
| Weight | 272 g |
| Dimensions | 210 x 42 x 14 mm |
| Standard | DIN 5254 B |
| REACH compliant | does not contain SVHC |
| RoHS compliant | not applicable |

Technical details

| | |
|-----------------|---------------|
| Size of shaft | Ø 40 – 100 mm |
| Tips (diameter) | 2.3 mm |

technical change and errors excepted





Spring inside the joint: the spring is protected inside the precisely bolted joint. It does not hinder work and cannot get dirty or lost.