

Product information

67 01 140

High Leverage End Cutting Nipper

DIN ISO 5748

- With cutting edges for soft, hard and piano wire
- High cutting capacity with little effort due to optimum coordination of cutting edge angle and transmission ratio
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 62 HRC
- Chrome vanadium heavy-duty steel, forged, multi stage oil-hardened



General

Article No.	67 01 140
EAN	4003773043690
Pliers	black atramentized
Head	polished
Handles	plastic coated
Weight	152 g
Dimensions	140 x 50 x 15 mm
Standard	DIN ISO 5748
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Cutting capacities soft wire (diameter)	Ø 4 mm
Cutting capacities medium hard wire (diameter)	Ø 3.1 mm
Cutting capacities hard wire (diameter)	Ø 2.0 mm
Cutting capacities piano wire (diameter)	Ø 1.5 mm

technical change and errors excepted

