

## **Product information**

## 70 02 160

## **Diagonal Cutter**

**DIN ISO 5749** 



- With elongated cutting edge
- The indispensable diagonal cutter for all-round use High-quality material and precise workmanship for long service life
- Precision cutting edges for soft and hard wire
- Clean cutting of thin copper wires, also at the cutting edge tips
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 62 HRC
- Narrow head style for use in confined areas
- With bevel
- Vanadium electric steel, forged, multi stage oil-hardened



General	
Article No.	70 02 160
EAN	4003773034032
Pliers	black atramentized
Head	polished
Handles	with multi-component grips
Weight	206 g
Dimensions	160 x 53 x 21 mm
Standard	DIN ISO 5749
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details	
Cutting capacities soft wire (diameter)	Ø 4.0 mm
Cutting capacities medium hard wire (diameter)	Ø 3.0 mm
Cutting capacities hard wire (diameter)	Ø 2 mm

technical change and errors excepted

