

Product information

70 02 180

Diagonal Cutter

DIN ISO 5749



- The indispensable diagonal cutter for all-round use
- High-quality material and precise workmanship for long service life
- Precision cutting edges for soft and hard wire
- Clean cutting of thin copper wires, also at the cutting edge tips
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 62 HRC
- Narrow head style for use in confined areas
- With bevel
- · Vanadium electric steel, forged, multi stage oil-hardened

General			
Article No.	70 02 180		
EAN	4003773034049		
Pliers	black atramentized		
Head	polished		
Handles	with multi-component grips		
Weight	252 g		
Dimensions	180 x 54 x 22 mm		
Standard	DIN ISO 5749		
REACH compliant	does not contain SVHC		
RoHS compliant	not applicable		
Technical details			
Cutting capacities soft wire (diameter)	Ø 4.0 mm		
Cutting capacities medium hard wire (diameter)	Ø 3.0 mm		
Cutting capacities hard wire (diameter)	Ø 2.5 mm		

technical change and errors excepted