

Product information

70 06 180 T

Diagonal Cutter

DIN ISO 5749 IEC 60900 DIN EN 60900



- Pliers with integrated, insulated tether attachment point for a tool tether
- The indispensable diagonal cutter for all-round use
- High-quality material and precise workmanship for long service life
- Precision cutting edges for soft and hard wire
- Clean cutting of thin copper wires, also at the cutting edge tips
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 62 HRC
- Narrow head style for use in confined areas
- Vanadium electric steel, forged, multi stage oil-hardened





General	
Article No.	70 06 180 T
EAN	4003773081470
Pliers	chrome-plated
Head	chrome-plated
Handles	insulated with multi-component grips, VDE-tested with integrated insulated tether attachment point for a tool tether
Weight	270 g
Dimensions	180 x 57 x 29 mm
Standard	DIN ISO 5749 DIN EN 60900 IEC 60900
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details	
Cutting capacities soft wire (diameter)	Ø 4.0 mm
Cutting capacities medium hard wire (diameter)	Ø 3.0 mm
Cutting capacities hard wire (diameter)	Ø 2.5 mm
Drop Protection System	yes
VDE tested	yes

technical change and errors excepted

KNIPEX Quality – Made in Germany





clean cutting of thin copper wires, also at the cutting edge tips