

Product information

70 11 110

Diagonal Cutter

DIN ISO 5749

- The indispensable diagonal cutter for all-round use
- High-quality material and precise workmanship for long service life
- Precision cutting edges for soft and hard wire
- Clean cutting of thin copper wires, also at the cutting edge tips
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 62 HRC
- Narrow head style for use in confined areas
- With bevel
- Vanadium electric steel, forged, multi stage oil-hardened



General

| | |
|-----------------|-----------------------|
| Article No. | 70 11 110 |
| EAN | 4003773018193 |
| Pliers | black atramentized |
| Head | polished |
| Handles | plastic coated |
| Weight | 91 g |
| Dimensions | 110 x 61 x 14 mm |
| Standard | DIN ISO 5749 |
| REACH compliant | does not contain SVHC |
| RoHS compliant | not applicable |

Technical details

| | |
|------------------------------------------------|----------|
| Cutting capacities soft wire (diameter) | Ø 3.0 mm |
| Cutting capacities medium hard wire (diameter) | Ø 2.0 mm |
| Cutting capacities hard wire (diameter) | Ø 1.2 mm |

technical change and errors excepted