

Product information

71 01 250

KNIPEX CoBolt® XL

Compact Bolt Cutter



- For powerful cutting of larger cross-sections as well as very hard materials
- Two-hand operation for maximum cutting force
- Straight cutting edges
- 60 % less effort required compared to conventional high-leverage diagonal cutters
- 40-fold increase of manual force due to special joint design
- With gripping surface below the joint for gripping and pulling wires from Ø 1.0 mm
- Induction-hardened precision blades: cutting edge hardness approx. 64 HRC
- Chrome vanadium heavy-duty steel, forged, multi stage oil-hardened



General

| | |
|-----------------|--------------------|
| Article No. | 71 01 250 |
| EAN | 4003773079637 |
| Pliers | black atramentized |
| Handles | plastic coated |
| Weight | 465 g |
| Dimensions | 250 x 55 x 20 mm |
| REACH compliant | contains SVHC |
| RoHS compliant | not applicable |

Technical details

| | |
|--|----------|
| Cutting capacities medium hard wire (diameter) | Ø 5.6 mm |
| Cutting capacities hard wire (diameter) | Ø 4.0 mm |
| Cutting capacities piano wire (diameter) | Ø 3.8 mm |

technical change and errors excepted

