

Product information

71 32 200 T

KNIPEX CoBolt®

Compact Bolt Cutter



- Opening spring and locking device are integrated in the handles also for comfortable work and protected transport
- With slim multi-component grips without collar for better handling and easier transport
- With gripping surface below the joint for gripping and pulling wires from Ø 1.0 mm
- Pliers with tether attachment point for mounting a fall protection system
- With precision cutting edges for soft, hard and piano wire
- Cuts bolts, nails, rivets, etc. up to Ø 5.2 mm
- Efficient joint design ensures exceptional cutting performance with little effort
- With recess for easier cutting of thicker wires
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 62 HRC
- Chrome vanadium heavy-duty steel, forged, multi stage oil-hardened



General

Article No.	71 32 200 T
EAN	4003773080060
Pliers	black atramentized
Handles	with slim multi-component grips, with integrated tether attachment point for a tool tether
Weight	380 g
Dimensions	200 x 55 x 23 mm
REACH compliant	contains SVHC
RoHS compliant	not applicable

Technical details

Cutting capacities soft wire (diameter)	Ø 6 mm
Cutting capacities medium hard wire (diameter)	Ø 5.2 mm
Cutting capacities hard wire (diameter)	Ø 4.0 mm
Cutting capacities piano wire (diameter)	Ø 3.6 mm
Drop Protection System	yes

technical change and errors excepted